

USB 5 Gbps Cable USB Type-A male to USB Type-A female for installation with M20 thread and protective cap IP68 dust and waterproof 50 cm black

Description

This USB cable by Delock can be used to connect various devices. The built-in jack can be attached, for e.g., to a housing with a suitable cut-out.

IP68 dust and waterproof

The sealing cap protects the USB female port from moisture, damage and dirt in outdoor areas.



60 cm

Item no. 88149

EAN: 4043619881499

Country of origin: China

Package: Zip poly bag

Technical details

- Connectors:
 - 1 x USB 5 Gbps Type-A male
 - 1 x USB 5 Gbps Type-A female for installation
- Thread size: M20
- Built-in hole Ø: 20.8 mm
- Cable gauge:
 - 28 AWG data line
 - 24 AWG power line
- Data transfer rate up to 5 Gbps
- Silicone sealing ring orange
- With sealing cap
- Cable diameter: ca. 5.5 mm
- Length incl. connectors: ca. 50 cm
- Operating temperature: -40 °C ~ 105 °C
- Protection class: IP68
- Housing material: PA66
- Colour: black

Package content

- USB 5 Gbps cable

Images



General

Protection class:	IP68
-------------------	------

Interface

Connector 1:	1 x USB 5 Gbps Type-A male
Connector 2:	1 x USB 5 Gbps Type-A female for installation

Technical characteristics

Data transfer rate:	5 Gbps
---------------------	--------

Physical characteristics

Housing material:	PA66
Cable gauge:	24 AWG
Length:	60 cm
Colour:	black
Cable diameter:	5.5 mm

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de