

Keystone Module RJ45 jack to RJ45 jack Cat.6A UTP white

Description

This module by Delock can be used to extend twisted pair cables. With its standardised dimensions it can be used for easy snap-in mounting in e.g. a Keystone patch panel, face plate or surface-mount box.



Item no. 90639

EAN: 4043619906390

Country of origin: China

Package: Zip poly bag

Technical details

- Connectors:
 - 1 x RJ45 jack
 - 1 x RJ45 jack
- Cat.6A specification
- UTP
- For Keystone ports with 19.2 x 14.9 mm
- Operating temperature: -25 °C ~ 70 °C
- Material: plastic
- Colour: white
- Dimensions (LxWxH): ca. 30.0 x 16.2 x 20.5 mm

Package content

- Keystone module

General

Specification:	Cat. 6A
Style:	both sides identical

Interface

Connector 1:	1 x RJ45 jack
Connector 2:	1 x RJ45 jack

Technical characteristics

Operating temperature:	-25 °C ~ 70 °C
------------------------	----------------

Physical characteristics

Material:	Plastic
Shielding:	unshielded
Length:	30.0 mm
Width:	16.2 mm
Height:	20.5 mm
Colour:	white

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de

