

# RJ45 Network Cable with braided coating Cat.6A U/FTP Slim 0.5 m blue

## Description

This network cable by Delock can be used to connect different networking devices, e.g. a NIC to a switch or a patch panel.

### Slim patch cable

The thin patch cables are characterised by their small cable diameter and enable flexible and space-saving cabling in the network cabinet.

### With braided jacket

The jacket provides excellent resistance to abrasion and protects the network cable from kinks and breaks. Thus, the cable remains durable.



**Item no. 80376**

EAN: 4043619803767

Country of origin: China

Package: Zip poly bag

## Technical details

- Connectors:  
1 x RJ45 plug  
1 x RJ45 plug
- Cat.6A specification
- Data transfer rate up to 10 Gbps
- Bandwidth: 500 MHz
- Shielded (U/FTP)
- Slim
- With braided jacket
- Cable gauge: 32 AWG
- Contacts gold-plated: 50 µm
- Cable diameter: ca. 4.1 mm
- Cable jacket material: nylon braid
- Colour: blue
- Length: ca. 0.5 m

## System requirements

- A free RJ45 jack

---

## Package content

- RJ45 cable

---

## Images



## General

Specification:	Cat. 6A
Style:	both sides identical

## Interface

Connector 1:	1 x RJ45 male
Connector 2:	1 x RJ45 male

## Physical characteristics

Cable gauge:	32 AWG
Material:	Nylon braid
Shielding:	U/FTP
Length:	0.5 m
Colour:	blue

## Manufacturer information

---

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de