

# USB 2.0 Cable USB Type-A male to USB Type-C™ male with extended bend protection 1 m

## Description

This USB cable by Delock enables the connection between a device with a USB Type-C™ connector and a PC or a laptop equipped with a free USB port.

## Quality

Optically the cable convinces with its fine textile shielding and connectors with metal housing. The long kink protection provides better strain relief and protects against excessive bending.

## Fast charging and power

The USB data and charging cable enables fast charging with its 60 W with a power bank or modern USB chargers. Quick Charge 3.0 is supported up to 20 V and 3 A.



**Item no. 81121**

EAN: 4043619811212

Country of origin: China

Package: Zip poly bag

## Technical details

- Connectors:
  - 1 x USB Type-A male
  - 1 x USB Type-C™ male
- Cable gauge:
  - 30 AWG data line
  - 22 AWG power line
- Fast Charging function: 20 V / 3 A (60 W)
- Cable diameter: ca. 4 mm
- Data transfer rate up to 480 Mbps
- Cable with textile shielding
- Connector with metal housing
- Colour: black / anthracite
- Length: ca. 1 m

## Package content

- USB 2.0 cable

## Images



## General

Specification:	USB 2.0 USB Type-C™
----------------	------------------------

## Interface

Connector 1:	1 x USB 2.0 Type-A male
Connector 2:	1 x USB 2.0 Type-C™ male

## Technical characteristics

Data transfer rate:	480 Mbps
Maximum current:	3 A

## Physical characteristics

Cable gauge:	30 AWG data line 22 AWG power line
Length:	1 m
Colour:	black

## Manufacturer information

---

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de