

GALERAS CLEAR



CLEAR POLYCARBONATE GOGGLES - INDIRECT VENTILATION

Ref. GALERVI



Product specifications

Polycarbonate goggles. Indirect ventilation. Flexible PVC and nylon frame. Panoramic screen. Adapted to wear with glasses and disposable respiratory half-masks. Wide elastic strap.

Frame : PVC

Screen : polycarbonate

COLOUR

Clear

SIZE

Adjustable

Product Use - Risks



Biological chemical particles



Shock



Second work / craftsman



Hygiene environment



Oil / Gas



Mining



Agriculture / Green areas



Construction / Civil engineering



Heavy industry

Product's highlights & user's benefits



Tilting elastic

Very good support

Marking (EN166)
1 = the best optical class
B = resistance to medium energy impacts
T = impact resistance at extreme temperatures
3 = resistance to liquid splashes
4 = resistance to large dust particles



Anti-mist



Anti-scratch



UV400

Certifications and Standards



REGULATION (EU) 2016/425

EN166:2001 Personal eye-protection - Specifications

1 BT: Oculars
34 BT: Frame

USA STANDARDS



ANSI Z87.1-2003 American National Standards Institute - Occupational and didactic Personal Eye and Face Protection Devices.
Z87+: Impact resistance

References

References	Bar code	COLOUR	SIZE
GALERVI	3295249137519	Clear	Adjustable