

# USB 2.0 Cable Type-A to USB Type-C™ with RGB illumination 1 m

## Description

This USB cable by Delock enables the connection between a device with a USB Type-C™ connector and a PC or a laptop equipped with a free USB port.

### RGB illumination

As soon as the cable is connected to a power source, the cable lights up in red and then changes to a soft colour gradient with eight different colours. The lighting is always discreet and inconspicuous.



**Item no. 88164**

EAN: 4043619881642

Country of origin: China

Package: Zip poly bag

## Technical details

- Connectors:
  - 1 x USB 2.0 Type-A male
  - 1 x USB Type-C™ 2.0 male
- Cable gauge:
  - 30 AWG data line
  - 22 AWG power line
- RGB illumination: smooth colour gradient in 8 different shades
- Host = USB Type-A; Device = USB Type-C™
- Output: 5 V / 3 A
- Data transfer rate up to 480 Mbps
- Colour: transparent / copper-coloured
- Length incl. connectors: ca. 1 m

## System requirements

- PC or laptop with a free USB Type-A port
- Device with USB Type-C™ port

## Package content

- Cable

---

## Images



## General

Specification:	USB 2.0
----------------	---------

## Interface

Connector 1:	1 x USB 2.0 Type-A male
Connector 2:	1 x USB 2.0 Type-CTM male

## Technical characteristics

Data transfer rate:	480 Mbps
Maximum current:	3 A
Voltage:	5 V

## Physical characteristics

Pin finishing:	gold-plated
Cable gauge:	30 AWG data line 24 AWG power line
Length:	1 m
Colour:	transparent

## Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de