

Coaxial High Speed HDMI cable HDMI male to Mini HDMI male 8K 60 Hz 3 m

Description

This High Speed HDMI with Ethernet cable by Delock enables the connection between a camera or tablet with Mini HDMI interface and a monitor or TV with an HDMI port.

By supporting a maximum bandwidth of 48 Gbps, content up to 8K Ultra HD (7680 x 4320 @ 60 Hz) resolution can be displayed.

Dynamic HDR and Dolby® Vision support

Supporting Dynamic HDR and Dolby® Vision, the cable is ideal for home cinema and gaming applications. Colours are realistically displayed with impressive depth, brightness and contrast are optimally reproduced.

Perfect sound with eARC support

The Delock HDMI cable supports Enhanced ARC (eARC). This allows HDMI devices such as Blu-ray players to be connected directly to the TV. The uncompressed audio signals are then transmitted directly and lossless to the connected sound system via the audio return channel.



Item no. 81686

EAN: 4043619816866

Country of origin: China

Package: Zip poly bag

Technical details

- Connectors:
 - 1 x HDMI male
 - 1 x HDMI Mini-C male
- Cable gauge: 30 AWG
- Cable type: coaxial
- Cable diameter: ca. 4.8 mm
- Triple shielded cable
- Contacts gold-plated
- Transmission of audio and video signals
- Data transfer rate up to 48 Gbps
- Resolution up to:
 - 7680 x 4320 @ 60 Hz
 - 5120 x 2880 @ 120 Hz
 - 3840 x 2160 @ 240 Hz
 (depending on the system and the connected hardware)
- Supports the 21:9 cinema aspect ratio
- Supports 1080p HFR (High Frame Rate) 3D

- Supports colour sampling in 4:4:4, 4:2:2 and 4:2:0 format
- Supports Display Stream Compression 1.2 (DSC)
- Supports Dolby® Vision
- Supports Dynamic HDR
- Supports Game Mode VRR
- Supports eARC
- Up to 32 audio channels for speakers
- Up to 1536 kHz audio sampling rate
- Supports Dolby® TrueHD and DTS-HD Master Audio™
- Supports dynamic adjustment of lip synchronicity for audio / video delays
- Supports CEC 2.0 control commands
- Colour: black
- Length incl. connectors: ca. 3 m

Package content

- HDMI cable

Images



General

Specification:	Display Stream Compression 1.2 Dolby® Vision Dynamic HDR eARC 21:9 cinema aspect ratio 1080p HFR (High Frame Rate) 3D colour sampling in 4:4:4, 4:2:2 and 4:2:0 format Game Mode VRR Dolby® TrueHD and DTS-HD Master Audio™ CEC 2.0 control commands
----------------	---

Interface

Connector 1:	1 x HDMI male
Connector 2:	1 x HDMI Mini-C male

Technical characteristics

Data transfer rate:	up to 48 Gbps
Maximum screen resolution:	7680 x 4320 @ 60 Hz 3840 x 2160 @ 240 Hz 5120 x 2880 @ 120 Hz

Physical characteristics

Cable category:	coaxial
Cable length incl. connectors:	3 m
Pin finishing:	gold-plated
Cable gauge:	30 AWG
Shielding:	triple
Colour:	black
Cable diameter:	4.8 mm

Manufacturer information

Street Beeskowdamm 13/15

Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de