

Technical Datasheet

tasker® C235 – 1x6,00 mm²

Unipolar Flexible Cable



A

B

CATEGORY Flexible Audio Cable (See Audio Catalogue)
APPLICATIONS Speakers and Hi-Fi Car Systems.

- A:** Soft **PVC** Sheath. Available in different color.
Outer cable diam. Ø 7,00 (±0,20) mm.
- B:** O.F.C. Red Copper formation 63x12x0,10 mm.
Wires stranded in beams and stranded again to create cores.
Nom. Cross section 1x6,00 mm².

MARKING **tasker® C 235 1x6,00 mm² O.F.C. Speaker Cable**
CUSTOM PRODUCTION This product may be custom produced also in **L.S.Z.H.** polymer, **PE** or **PUR**.

Cable Properties

Conductor Resistance	2,75 Ω/Km
Max Rated Voltage	49 V
Operative Temperature	-15/+70°C

USE	X	Indoor	Interno Edificio	INSTALLATION	X	Fixed	Fissa	INFORMATION	X	RoHS2 Compliant
Impiego		Outdoor Limited	Esterno Limitato	Posa	X	Restricted Mobile	Mobile Limitata	Informazioni	X	Ver. A / 16.05.17
		Outdoor	Esterno			Mobile	Mobile			
		Outdoor Direct Burial	Esterno Interrato			Mobile in Drag Chain	Mobile in Catena			