

PRODUCT-DETAILS

TC5142-NDT

SADDLE SPRT BASE .9X.6IN DETEC NYL



General Information

Extended Product Type	TC5142-NDT
Product ID	7TAG009660R0019
EAN	5415022188288
Catalog Description	SADDLE SPRT BASE .9X.6IN DETEC NYL
Long Description	Saddle Support Mounting Base, Detectable Blue Nylon, Length of 23.4mm (0.92 Inches), Width of 14.2mm (0.56 Inches), Screw Mounting Method, #10 Pan Head Screw, Mounting Hole Size of 5.2mm (0.20 Inches), 100 Pack

Ordering

EAN	5415022188288
UPC	786209019592
Country of Origin	United States (US) United Kingdom (GB)
Customs Tariff Number	3926909985
Selling Unit of Measure	each

Container Information

Package Level 1 Units	100 piece
Package Level 1 Width	5 in 127 mm
Package Level 1 Height	1 in 25 mm
Package Level 1 Depth / Length	9 in 229 mm
Package Level 2 Units	500 piece

Package Level 2 Width	9 in 229 mm
Package Level 2 Height	5 in 127 mm
Package Level 2 Depth / Length	9.5 in 241 mm

Additional Information

Brand / Label	Ty-Rap
Color	Blue
Effective Date	20120926
Material	Nylon/Polyamide 6.6
Mounting Type	Screw
Process Temperature Rating	-40 to +185 °F
Product Name	PLASTIC MOUNTING BASE
Product Type	Saddle Support Base
Special Functions	Detectable with metal and X-ray detection equipment.

Certificates and Declarations (Document Number)

Data Sheet, Technical Information	TC5142-NDT
Instructions and Manuals	TC5142-NDT
REACH Declaration	9AKK107992A3997
RoHS Information	9AKK107991A8364

Classifications

ETIM 6	EC000449 - Mounting base and -element for cable ties
ETIM 7	EC000449 - Mounting base and -element for cable ties
ETIM 8	EC000449 - Mounting base and -element for cable ties
UNSPSC	39121717
WEEE Category	Product Not in WEEE Scope
IDEA Granular Category Code (IGCC)	5065 >> Cable tie mounts

Categories

Low Voltage Products and Systems → Installation Products → Wire Management and Connectivity → Cable Ties

