



BETA 1233MQF/D4-FX

Set of four slim screwdrivers with electrician's scissors 1128FX



Features

The new set has been designed and conceived to provide you with the best tools, guaranteeing excellent performance in every situation.

PERFECT GRIP AND ANTI-ROLL

The embossed texture of the new giraité, combined with the TPU material for greater adhesion, ensures a secure grip even in the most difficult conditions, while the enlarged handle optimises ergonomics, ensuring a stable and comfortable grip during the most precise operations.

PERFECT GRIP AND ANTI-ROLL

The embossed texture, combined with the TPU material for increased adhesion, ensures a secure grip even in the most difficult conditions, while the enlarged handle optimises ergonomics, ensuring a stable and comfortable grip during the most precise operations.

LARGE SECTION CABLE CUTTER THROAT

The integrated groove in the 1128FX electrician's scissor allows cables with cross-sections up to 50 mm² to be cut with ease and safety.



SLIM TECHNOLOGY

Slim technology reduces the blade diameter without altering the thickness of the insulator, improving convenience without compromising safety.



SLIM HANDLE

The slim handle ensures a secure and comfortable grip, offering greater manoeuvrability even in tight spaces.



FLAT CAP AND RECOGNITION

The flat handle at the end offers more thrust and facilitates identification due to the size imprint.

1128FX:

n. 1

1234MQF/LP:

n. 2 Screwdrivers for headless slotted screws 0,8X4-1,0X5,5 mm

1232MQF:

n. 2 Screwdrivers for cross head Phillips® screws PH1-PH2

Coded items

	Art.
012330905	1233MQF/D4-FX



1833XS/2

LED inspection torch, made of sturdy anodized aluminium

Features:

- 200 lumens
- Adjustable focus
- Batteries: 2xAAA (not included)
- IP66
- Battery life: 10.0h
- Lighting range: 112 m



	art.	L mm	g
018330001	1833XS/2	133	53





BETA 1169MQ/D2

Assortment of insulated combination pliers (1 pcs.) and insulated diagonal cutting nippers



Certifications and Standards



Features

The 1,000V insulated tools set consists of combination pliers and diagonal cutting nippers to combine functionality and safety.

SAFETY

Each tool undergoes rigorous safety checks, ensuring maximum protection when working on live equipment up to 1,000V AC and 1,500V DC.

MECHANICAL PERFORMANCE

Beta insulated tools offer a high level of safety without sacrificing mechanical performance, comparable to non-insulated tools. This allows operators to work efficiently and precisely, while guaranteeing maximum protection.



INSULATION 1,000V

The handles are designed and tested for maximum operator safety.



INDISPENSABLE

The insulated diagonal cutting nippers and pliers are indispensable tools for any professional who needs to work with maximum safety.

Certifications and Standards



1150MQ: n. 1 combination pliers 1000V □ 180 mm
1082MQ: n. 1 diagonal cutting nippers 1000V □ 160 mm

Coded items

	Art.	
011690152	1169MQ/D2	1150MQ 180 mm 1082MQ 160 mm



1128FX

electrician's scissors, straight stainless steel blades, with microteeth, cable cutting groove and crimping pliers for tube terminals

- Articulated belt hook case
- Bimaterial handles
- Anti-loose pin

With cable cutting and crimping function

	art.	L mm	L1 mm	A mm	B mm	$\frac{mm^2}{mm^2}$	$\frac{g}{g}$
011280090	1128FX	145	52	22	17	50	80

