

TSL-CAM-WRHD-01

## Smart rotating wifi camera, E27, 1080p

### SMART HOME, SMART LIFE

- 1080p Full High Definition video
- Quick installation in any free E27 light socket
- Works with free Tuya SmartLife app: your personal smart home control hub
- Perfect for monitoring your office, home, warehouse, etc.



### Specifications

WiFi standard: 802.11 b/g/n  
 Frequency Range 2.4 GHz ~ 2.4835 GHz, antenna gain 3 dBi  
 Max. Transmit power: 17.68 dBm (802.11b)  
 Sensor: CMOS 2 Mega pixels  
 Viewing angle: 120°  
 Lens type/specs: 1/2.9", 3.6 mm lens system, F = 2.0  
 Video format: H.264 AVI  
 Supported resolutions: max. 1920 x 1080  
 Sound SNR: 48 dB  
 Built-in speaker  
 Built-in IR backlight and IR-CUT filter  
 MicroSD card up to 128 GB supported  
 AC power consumption: 100-240 V AC, 50/60 Hz, max 0.5 A  
 AC power connection: E27 lamp socket  
 Dimensions: 155 mm x 50 mm x 50 mm  
 Weight: 0.3 kg  
 Operating conditions: 0-55 Celsius degrees at 10-90% humidity

FOR INDOOR USE ONLY

### Features

- Indoor 1080p smart wifi-camera with built-in microphone and speaker
- Smart: Works via the Tuya smarthome platform easy smart control via the SmartLife app
- Universal: Can be embedded in any existing Tuya based smart home solution and combined with any other Tuya compatible products
- Easy and quick installation in a standard E27 light socket
- Practical microSD slot for easy video recording and capturing snapshots

### Packaging

Q'ty in crtn, pcs	50
Crtn volume, CUM	0.082215
Crtn weight, kgs	15.3
Individual package size LxWxH:	135x105x100 mm
Carton size LxWxH:	540x290x525 mm
Country of origin	CN
Barcode	8716309126427
Customs code	8525810000

### Package contents

Camera  
User Manual

### Certificates



### System requirements

Free E27 lamp socket  
TUYA App: Android or iOS smartphone