

USB Type-C™ Docking Station 4K - HDMI / DP / USB / SD / LAN / PD 3.0

Description

This docking station by Delock can be connected to a computer with a USB-C™ DP Alt Mode or Thunderbolt™ 3 port and provides a variety of interfaces. Two monitors can be operated simultaneously at the **DisplayPort** and **HDMI** outputs. Three built-in USB ports allow the use of peripherals, and connections for **Gigabit network**, as well as an **SD** card reader, complete the features.



Item no. 87683

EAN: 4043619876839

Country of origin: China

Package: Retail Box

Multi-Stream Transport (MST)

The product is an MST hub and supports the extended desktop configuration of DisplayPort. This allows multiple monitors to be combined into one large display. Thereby the docking station supports a maximum resolution of up to **1080p** per monitor.

USB Power Delivery (USB PD 3.0) support up to 100 watt

The docking station has a **USB Type-C™ Power Delivery** port to connect the power supply of the laptop or tablet to charge it. In addition it also supplies the USB ports with power. The docking station can also be used without a power supply.

Small sturdy helper

Due to its **small dimensions** and its **sturdy housing**, this Delock docking station is particularly suitable for travelling. It can simply be packed into the bag together with the laptop or tablet and used as needed.

Technical details

- Connectors:
 - 1 x USB Type-C™ male
 - 1 x USB 5 Gbps USB Type-C™ female
 - 2 x USB 5 Gbps Type-A female - Battery Charging specification BC1.2
 - 1 x SD / SDHC / SDXC slot
 - 1 x HDMI-A female
 - 1 x DisplayPort female

- 1 x Gigabit LAN 10/100/1000 Mbps RJ45 jack
- Resolution up to 3840 x 2160 @ 30 Hz
(depending on the system and the connected hardware)
- Transmission of audio and video signals
- Functions: Mirrored or Extended (Windows only)
- Supports HDCP 1.4
- Input power: 1 x USB Type-C™ female max. 100 W
- Metal housing
- Cable length without connectors: ca. 20 cm
- Colour: grey
- Dimensions (LxWxH): ca. 117 x 60 x 16 mm

System requirements

- Chrome OS 68.0 or above
- Mac OS 10.13.3 or above
- Windows 7/7-64/8.1/8.1-64/10/10-64/11
- Device with a free USB Type-C™ port and DisplayPort alternate mode or with a free Thunderbolt™ 3 port

Package content

- USB-C™ docking station
- User manual

Images



General

Supported operating system:	Chrome OS Mac OS 10.13.3 or above Windows 10 32-Bit Windows 10 Mobile Windows 7 32-Bit Windows 7 64-Bit Windows 8.1 32-Bit Windows 8.1 64-Bit
-----------------------------	--

Technical characteristics

Maximum screen resolution:	3840 x 2160 @ 30 Hz
----------------------------	---------------------

Physical characteristics

Cable length:	20 cm (without connector)
Length:	117 mm
Width:	60 mm
Height:	16 mm
Colour:	grey

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de