BAHCO




2628 GC-180IP

ERGO™ Combination Pliers with Self-Opening Dual-Component Handles and Chrome Finish (180 mm) Industrial Pack

PRODUCT DETAILS

- Two-component ERGO™ handles: soft thermoplastic surface on tough polypropylene base provides superior grip
- Developed according to the scientific ERGO™ process
- Cutting capacity: 2 mm to 3 mm iron alloy, 1.8 mm to 2.5 mm piano wire
- Equipped with a patented return spring featuring an on/off function
- Gripping surfaces particularly suited for flat and round material
- Special head design for better accessibility, with hardened cutting edges for cutting soft and hard wire
- High-performance alloy steel
- Chrome plated finish, anti-corrosion treated
- Standards: ISO 5746
- IP = Industrial packaging

PATENTED



Follow the Fish!

PRODUCT ATTRIBUTES

Product	A	B	C	D	E	F	G	Fe+	Piano	g
2628 GC-180IP	180 mm	36 mm	24 mm	10.8 mm	4 mm	10.8 mm	14 mm	2.5 mm	2.0 mm	240 g