

FPC Flat Ribbon Cable USB Type-C™ to HDMI (DP Alt Mode) 4K 60 Hz 13.5 cm

Description

This cable by Delock enables the connection of an HDMI monitor to a PC or laptop with USB-C™ or Thunderbolt™ 3 port, such as a MacBook or a Chromebook. The interface has to support the DisplayPort Alternate Mode.

Ultra flexible cable

The cable is characterized by its special construction. Instead of normal copper wires there is a flexible circuit board inside the cable, which is also called FPC (Flexible Printed Circuit). This makes the cable extremely flexible and yet robust.



Item no. 86729

EAN: 4043619867295

Country of origin: China

Package: Zip poly bag

Technical details

- Connectors:
1 x USB Type-C™ male >
1 x HDMI female
- Chipset: Realtek RTD2172U
- DisplayPort 1.2 and High Speed HDMI with Ethernet (HEC) specification
- FPC (Flexible Printed Circuit) flat ribbon cable
- Cable thickness: ca. 3 mm
- Resolution up to 3840 x 2160 @ 60 Hz
(depending on the system and the connected hardware)
- Transmission of audio and video signals
- Supports 3D displays
- Supports HDR
- Supports HDCP 1.4 and 2.2
- USB bus powered
- Plug & Play
- Colour: silver / black
- Length incl. connectors: ca. 13.5 cm

System requirements

- Mac OS 10.15.6 or above

- Windows 10/10-64
- iPad Pro (2018)
- PC or laptop with a free USB Type-C™ port and DisplayPort alternate mode or
- PC or laptop with a free Thunderbolt™ 3 port

Package content

- USB-C™ to HDMI cable

Images



General

Specification:	DisplayPort 1.2 HDCP 1.4 HDCP 2.2 HDMI 2.0 HDR
Supported operating system:	Mac OS 10.15.6 or above Windows 10 32-Bit Windows 10 64-Bit
Style:	Flat cable

Interface

Connector 1:	1 x USB Type-C™ male
Connector 2:	1 x HDMI-A female

Technical characteristics

Chipset:	Realtek RTD2172U
Maximum screen resolution:	3840 x 2160 @ 60 Hz

Physical characteristics

Length:	13.5 cm
Colour:	black

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de