

Automatic AC voltage regulator and stabilizer, LED, 220 V AC, 500 VA

EG-AVR-0501

ULTIMATE DEFENCE

- Protects valuable equipment
- Protects users



Features

- Automatic AC output voltage regulator (AVR) and stabilizer
- Pure sinusoidal AC wave form
- LED status indication
- Short circuit, over-voltage, over-load, over-heating protection

Packaging

Q'ty in crtn, pcs	8
Crtn volume, CUM	0.048
Crtn weight, kgs	18
Individual package size LxWxH:	190x180x175 mm
Carton size LxWxH:	390x365x340 mm
Country of origin	CN
Barcode	8716309068727
Customs code	8504408590

Certificates



Specifications

Technology: transformer, relay type
 Input voltage: 140 ... 270 V AC
 Input frequency: 50 Hz
 Output voltage: 220 V AC $\pm$ 8 %, sinusoidal wave form
 Output power: 500 VA (300 W)
 Efficiency: 98 %
 Sockets: IEC input and IEC output socket with Schuko input power cord
 Phase: single phase
 Display: LED type
 Circuit protection: circuit breaker
 Operating temperature: 0 ... 40 Celsius degrees
 Storage temperature: -15 ... 45 Celsius degrees
 Operating relative humidity: 10 ... 102 %RH, non-condensing
 Power cord: 1.2 m
 Dimensions: 130 x 140 x 123 mm
 Net weight: 2.15 kg