

RJ45 Slim Network Cable Cat.6A U/FTP angled black 5 m

Description

This network cable by Delock can be used to connect different networking devices, e.g. a NIC to a switch or a patch panel.

With angled connectors

The connectors can be angled in any direction, e.g. to the right, left, up or down. They also allow space-saving installation in narrow places.

Slim patch cable

The thin patch cables are characterised by their small cable diameter and enable flexible and space-saving cabling in the network cabinet.



5 m

Item no. 80937

EAN: 4043619809370

Country of origin: China

Package: Zip poly bag

Technical details

- Connectors:
 - 1 x RJ45 plug
 - 1 x RJ45 plug
- Cat.6A specification
- Data transfer rate up to 10 Gbps
- Bandwidth: 500 MHz
- Shielded (U/FTP)
- Slim
- Maximum angle: 60°
- Cable gauge: 32 AWG
- Connectors gold-plated: 50 µ"
- Cable diameter: ca. 3.8 mm
- Cable jacket material: LSZH (halogen-free)
- Operating temperature: -20 °C ~ 60 °C
- Colour: black
- Length: ca. 5 m

Package content

- RJ45 cable

Images



General

Specification:	Cat. 6A
Style:	both sides identical

Interface

Connector 1:	1 x RJ45 male
Connector 2:	1 x RJ45 male

Technical characteristics

Operating temperature:	-20 °C ~ 60 °C
------------------------	----------------

Physical characteristics

Cable gauge:	32 AWG
Material:	LSZH (halogen-free)
Shielding:	U/FTP
Length:	5 m
Colour:	black
Cable diameter:	3.8 mm

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de