

USB 2.0 Cable Type-A male to USB Type-C™ male rotatable with Fast Charging 60 W 1.2 m

Description

This USB cable by Delock enables the connection between a device with a USB Type-C™ connector and a PC or a laptop equipped with a free USB port.

Fast charging and power

The **USB data and charging cable** enables fast charging with its **60 W** with a power bank or modern USB chargers. Quick Charge 3.0 is supported up to 20 V and 3 A.

Rotatable plugs

The plugs on this cable are both **rotatable** and can be changed to ca. **110° angled plugs**, making them the ideal solution if there is a lack of space, for example. The plugs can also be rotated while they are plugged in.



1.2 m

Item no. 80769

EAN: 4043619807697

Country of origin: China

Package: Zip poly bag

Technical details

- Connectors:
 - 1 x USB 2.0 Type-A male
 - 1 x USB 2.0 USB Type-C™ male
- Cable gauge:
 - 30 AWG data line
 - 22 AWG power line
- Fast Charging function: 20 V / 3 A (60 W)
- Cable diameter: ca. 3 mm
- Data transfer rate up to 480 Mbps
- Colour: black
- Length: ca. 1.2 m

Package content

- USB 2.0 cable

Images



General

| | |
|----------------|------------------------|
| Specification: | USB 2.0 USB Type-C™ |
|----------------|------------------------|

Interface

| | |
|--------------|--------------------------|
| Connector 1: | 1 x USB 2.0 Type-A male |
| Connector 2: | 1 x USB 2.0 Type-C™ male |

Technical characteristics

| | |
|---------------------|----------|
| Data transfer rate: | 480 Mbps |
| Maximum current: | 3 A |

Physical characteristics

| | |
|--------------|---------------------------------------|
| Cable gauge: | 30 AWG data line 22 AWG power line |
| Length: | 1.2 m |
| Colour: | black |

Manufacturer information

| | |
|-------------|-------------------|
| Street | Beeskowdamm 13/15 |
| Postal code | 14167 |
| City | Berlin |
| Country | Deutschland |
| E-Mail | info@delock.de |
| Website | www.delock.de |