

CABLE CUTTERS

► Cable cutters

for copper and aluminium cables, two-colour multilayer immersion insulation, adjustment joint
Material tool steel



15-501 VDE

Art.-No.	Handle type	Type	Total length	Weight in g	1000 V
15-501 VDE	two-colour dip insulated	up to Ø 20 mm / 60 mm ²	210	360	  

► Ratchet cable cutters

for easier cutting of large cross-sections, for copper and aluminium cables, not for armoured cables.



15-506 VDE

Art.-No.	Handle type	Type	Total length	Weight in g	1000 V
15-506 VDE	two-colour dip insulated	up to Ø 32 mm / 240 mm ²	250	800	

VDE TOOLS

► Adjustable spanner

According to DIN 3117, IEC 60900:2004, two-colour multilayer dip insulation, 1000 V, jaw position 15°, with scale graduation

Art.-No.	Width across flats	Weight in g	1000 V
16-773 VDE	0-26	300	
16-774 VDE	0-30	500	



► Insulating protective gloves

for work under voltage up to 1000 Volt, made of natural latex high elasticity
piece tested according to DIN EN 60903, VDE 0682-part 31 1, test voltage 5000 Volt

Art.-No.	Type	Thickness	Length	Weight in g	1000 V
17-501 VDE	Größe 10	1.6 mm	360 ± 15 mm	175	KL. 0



17-501-VDE

► NH plug-in-grip

with leather cuff 380 x 220 mm for inserting or removing NH fuse links

Art.-No.	Type	Weight in g	1000 V
17-521 VDE	Siemens-handle for NH fuses 00-3, protection of forearm at higher currents (arc fault due to system)	450	



17-521-VDE

► Plastic clip

for fixing cover cloths, made of sturdy plastic with concealed spring and rubber web to prevent slipping

Art.-No.	Type	Length	Weight in g	1000 V
17-523 VDE	Clamping width 15 mm, opening width 40 mm	160 mm	60	



17-523-VDE

► Self-clamping sleeves

Protect against contact with a live cable end

Art.-No.	Type	Weight in g	1000 V
17-551 VDE	Ø 10 x 80 mm	20	



17-552 VDE