

VKA01034
CONNECTION TECHNOLOGY • CABLE SOCKETS / CONNECTORS PRE-ASSEMBLED ON ONE SIDE

, 10m, MC Female (socket) 3pin Straight, Free conductor end,
3x0.34mm², Ø5mm, 250V, IP67


MECHANICAL FEATURES

Cable infeed of A connection	Straight
Cable length	10 m
Degree of protection (IP)	IP67
Number of cores	3
Perm. ambient temperature of cable, fixed cable	-25 °C ... 80 °C
Suitable for trailing chain	+
Version	Connection cable
Wire assembly	19 x 0.16mm
Wire cross section	0.34 mm ²

ELECTRICAL FEATURES

Flow resistance	5 mOhm
Line diameter	5 mm
Number of pins of A connection	3
Rated current	4 A
Rated voltage	250 V
Type of A electrical connection	MC
Type of B electrical connection	Free conductor end
Type of plug-in contact, A connection	Female (socket)
With LED display	-

OTHER FEATURES

IR-networked	-
--------------	---

Other

Packaging dimensions	230mm x 50mm x 280mm
Shipping weight	0.38kg
Tariff code	85444290

Classification

ipf product group	850
eClass 8.0	27279218
eClass 9.0	27060311
eClass 9.1	27060311
ETIM-5.0	EC001855
ETIM-6.0	EC001855
ETIM-7.0	EC001855

Connection**Dimensional drawing****Installation**

Mounting / installation may only be carried out by a qualified electrician!

Disposal**Safety warnings**

Before initial operation, please make sure to follow all safety instructions that may be provided in the product information.

Never use these devices in applications where the safety of a person depends on their functionality.

LED lighting systems can generate intensive UV radiation, which can damage your eyes in case of improper use. The manufacturer cannot be held responsible for damages that result from improper use or connection.