

**BN 500****Vis de poêliers**

à fente

INOX A2



Toutes les longueurs avec filetage ~ sous tête

Article#	d ₁	d ₂ max.	k max.	n	t min.	L
1578022	M3	7	2	0,8	1	5
1578030						6
1578057						8
1578103						10
1578154						12
1578189						16
3059854						20
1578227	M4	10	2,2	1,2	1	5
1578235						6
1243160						8
1243179						10
1243187						12
1243195						16
1243209						20
1243217						25
1171291						30
1171305						35
3059855						40
1243225	M5	12,5	2,7	1,2	1,2	8
1243233						10
1243241						12
1243268						16
1243276						20
1243284						25
1243292						30
3059856						35

Article#	d ₁	d ₂ max.	k max.	n	t min.	L
3059857	M5	12,5	2,7	1,2	1,2	40
8306346						50
8306354						60
1243314	M6	15	3,3	1,6	1,5	8
1243322						10
1243330						12
1243349						16
1243357						20
1243365						25
1243373						30
1409069						35
3059858						40
8306362						45
8182582						50
8043140						60
8306370						70
5519951	M8	20	4,4	2	2	12
1409077						16
1210610						20
1210629						25
1243403						30
5514549						35
1243438						40
3059861						50
8182698						60
8306389						70
8306397						80