

Cable USB 2.0 Type-A male > USB 2.0 Type-A female ShapeCable 0.15 m

Description

This cable by Delock can be used to extend a USB connection and to connect various devices. Due to an integrated wire the ShapeCable can be bent into any form and retains its shape.



Item no. 83497

EAN: 4043619834976

Country of origin: China

Package: Zip poly bag

Technical details

- Connectors:
 - 1 x USB 2.0 Type-A male >
 - 1 x USB 2.0 Type-A female
- ShapeCable: integrated, shapeable wire
- Cable gauge:
 - 28 AWG data line
 - 24 AWG power line
- Cable diameter: ca. 5 mm
- Colour: black
- Length incl. connectors: ca. 0.15 m

System requirements

- A free USB port

Package content

- USB 2.0 extension cable

Images



Interface

Connector 1:	1 x USB 2.0 Type-A male
Connector 2:	1 x USB 2.0 Type-A female

Technical characteristics

Data transfer rate:	USB 2.0 up to 480 Mb/s
---------------------	------------------------

Physical characteristics

Cable gauge:	28 AWG data line 24 AWG power line
Length:	0.15 m
Colour:	black
Cable diameter:	5 mm

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de