

D-Type Module USB 5 Gbps Type-A female to USB 5 Gbps Type-A female with protective cap IP67 dust and waterproof

Description

This module by Delock can be mounted e.g. in panels or cases with D-type openings for XLR jacks. This makes it ideal for integrating digital equipment into professional audio systems.

IP67 dust and waterproof

The coupler offers increased protection from dirt and moisture for the connection of the cables.



Item no. 86971

EAN: 4043619869718

Country of origin: China

Package: Zip poly bag

Technical details

- Connectors:
 - 1 x USB 5 Gbps Type-A female
 - 1 x USB 5 Gbps Type-A female
- For D-type ports with 31 x 25 mm
- Panel cut-out (diameter): ca. 24 mm
- Data transfer rate up to 5 Gbps
- Protection class: IP67
- With sealing cap
- Two mounting holes for screw fastening
- Material: plastic
- Colour: black
- Dimensions (LxWxH): ca. 32.4 x 31.0 x 26.0 mm

Package content

- D-Type module

Images



General

Mounting type:	D-Type
Style:	both sides identical

Interface

Connector 1:	1 x USB 5 Gbps Type-A female
Connector 2:	1 x USB 5 Gbps Type-A female

Physical characteristics

Material:	Plastic
Length:	32.4 mm
Width:	31.0 mm
Height:	26.0 mm
Colour:	black

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de

