




Fibre optic diffuse reflection sensor

FT-00-A-A-M6/1M



Application

Function principle	Diffuse reflection sensor
Application	High temperature resistance; Robust design for use in harsh industrial environments

Detection zone

Range with fibre optic amplifier type	OKF; OUF; OOF; OCF
---------------------------------------	--------------------

OCF

Range fibre optics [mm]	330
-------------------------	-----

OKF

Range fibre optics [mm]	40
-------------------------	----

OOF

Range fibre optics [mm]	200
-------------------------	-----

OUF

Range fibre optics [mm]	40
-------------------------	----

Operating conditions

Ambient temperature [°C]	-40...290
--------------------------	-----------

Mechanical data

Weight [g]	59.5
Version of sensing head	straight
Sensing head thread	M6

E20071



Fibre optic diffuse reflection sensor

FT-00-A-A-M6/1M

Sensing head length	[mm]	35
Total length	[mm]	1000
Min. bending radius	[mm]	20; (for fixed installation)
Fibre arrangement		①
Materials		Adapter: ABS
Fibre material		glass
Fibre head material		aluminium
Fibre sheath material		aluminium

Accessories

Items supplied	hexagon nuts: 2 x M6, stainless steel
	tooth lock washers: 2
	knurled nut: 1 x M11

Remarks

Pack quantity	1 pcs.
---------------	--------