



FP BF 18



- Ventilation flange
- (recommended) alignment: vertical

CONNECTION DATA

MECHANICAL PROPERTIES

Delivered accessories:	Fastening material
IP degree of protection:	IP44
Suitable for box wall:	180 mm
(Recommended) alignment:	Vertical

AMBIENT CONDITIONS

Application area:	Indoor installation
Maximum ambient temperature 24 h:	35 °C
Ambient temperature:	-5 °C up to +40 °C
Relative humidity:	≤ 50 % at 40 °C, ≤ 100 % at 25 °C

DIMENSIONS

Height:	180 mm
Width:	33 mm
Depth:	33 mm
Net weight:	0.14 kg

CERTIFICATES

conforming to the standards:

IEC 61439-3

SALES DATA

Product number:

68000194

EAN:

4012591117827

Pack unit:

1

Customs tariff number:

85371098

ETIM class:

DYNAMIC: EC000331 - Ventilation plate (enclosure/cabinet)

ETIM-9.0: EC000331 - Ventilation plate (enclosure/cabinet)

ETIM-8.0: EC000331 - Ventilation plate (enclosure/cabinet)

ETIM-7.0: EC000331 - Ventilation plate (enclosure/cabinet)

ETIM-6.0: EC000331 - Ventilation plate (enclosure/cabinet)

ETIM-5.0: EC000331 - Ventilation plate (enclosure/cabinet)

ETIM-4.0: EC000331 - Ventilation plate (enclosure/cabinet)

DRAWINGS

