



A circular logo with a green border. The text "RoHS" is prominently displayed in the center in a large, bold, sans-serif font. Below "RoHS", the word "Compliant" is written in a smaller, italicized font. The outer ring of the logo contains the text "Amphenol Technology (Zhuhai) Co., Ltd." at the top and "2011/65/EU PBT" at the bottom.

MFG PART NUMBER: C10-730188-() () () ()

CODE NUMBER REFERENCE: SLPPB () B () () ()

ITEM	DESCRIPTION	CODE NUMBER	MFG NUMBER
COLOR	ORANGE	O	0
	BLACK	B	1
	RED	R	2
WIRE RANGE	50 MM2 CRIMPING	50	0
	35 MM2 CRIMPING	35	3
	25 MM2 CRIMPING	25	2
SEALING	IP67(MATED)	S	0
	NO SEALING	N	1
KEYWAY (Y°)	NO KEYWAY	BLANK	BLANK
	90°	0	0
	180°	1	1
	60°	2	2
	120°	3	3
	150°	4	4

SPECIFICATIONS	
CURRENT RATING	120A MAX FOR 25MM2 150A MAX FOR 35MM2 200A MAX FOR 50MM2
OPERATING VOLTAGE	1000V DC
OPERATING TEMPERATURE	-40°C - 125°C
CONTACT RESISTANCE	0.3 mΩ

N/A	PRO/ENGINEER INFORMATION
NEXT ASSEMBLY	Pro/e Model Used: 10-730188-000.ASSEM
METRIC DOCUMENT	Drawing Name: 10-730188.CUS

METRIC DOCUMENT

2. IF CHOOSE NO SEALING TYPE, THERE WILL BE NO O-RINGS AND GROMMET.

1. THE REFERENCED PRODUCT IS IN COMPLIANCE WITH THE MAXIMUM CONCENRATION
VALUES (MCVS) AS SET BY RoHS 2.0 DIRECTIVE 2011/65/EU
AND ANNEX II AMENDMENT DIRECTIVE (EU) 2015/863.

NOTES:

THIS DOCUMENT CONTAINS PROPRIETARY INFORMATION AND
SUCH INFORMATION MAY NOT BE DISCLOSED TO OTHERS FOR
ANY PURPOSE OR USED FOR MANUFACTURING PURPOSES
WITHOUT WRITTEN PERMISSION FROM THE AMPHENOL CORP.

N/A

NEXT ASSEMBLY

DOCUMENT NO.
C10-730188-()

SHEET 1 OF 1

REV
I

3

2

D

2

.571

SHEET 1 OF 1

C10-730188-()

A