

## Han CGM-P-EXi M25 D 9...16mm



Part number	19 00 000 7104
Specification	Han CGM-P-EXi M25 D 9...16mm
HARTING eCatalogue	<a href="https://b2b.harting.com/19000007104">https://b2b.harting.com/19000007104</a>

### Identification

Category	Accessories
Series of hoods/housings	Han <sup>®</sup> CGM-Ex i
Type of accessory	Cable gland

### Version

Field of application	Intrinsically safe electric circuits
----------------------	--------------------------------------

### Technical characteristics

Limiting temperature	-40 ... +100 °C
Tightening torque	≤5 Nm (depending on the cable and the seal insert used)
Wrench size	33
Degree of protection acc. to IEC 60529	IP68 IP69 / IPX9K acc. to ISO 20653
Size	M25
Clamping range	9 ... 16 mm
Width across corners	33.5 mm

### Material properties

Material (seal)	NBR
Material (cable glands)	Polyamide (PA)
Colour (accessories)	RAL 5012 (light blue) RAL 9005 (jet black)
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant



Pushing Performance

## Material properties

China RoHS	e
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	No

## Specifications and approvals

Approvals	DNV GL
-----------	--------

## Commercial data

Packaging size	1
Net weight	23.38 g
Country of origin	Germany
European customs tariff number	39269097
eCl@ss	27144432 Screwed cable gland (electr.)