

AL000031
CONNECTION TECHNOLOGY • CABLE SOCKETS / CONNECTORS PRE-ASSEMBLED ON ONE SIDE

accessories, fiber optic, cable, 5m, Blade terminal Female (socket)
 4pin Straight, Free conductor end, 4wire, PUR (Polyurethane),
 Ø3mm, Plastic, Welding area


MECHANICAL FEATURES

Ambient temperature	-10 °C ... 55 °C
Cable infeed of A connection	Straight
Cable length	5 m
Housing material	Plastic
Material of cable sheath	PUR (Polyurethane)
Number of cores	4
Perm. ambient temperature of cable, flexible cable	-10 °C ... 55 °C
Suitable for trailing chain	+
Version	Connection cable

ELECTRICAL FEATURES

Line diameter	3 mm
Number of pins of A connection	4
Type of A electrical connection	Blade terminal
Type of B electrical connection	Free conductor end
Type of plug-in contact, A connection	Female (socket)

OTHER FEATURES

Flame retardant	No
Welding area	+

Other

Packaging dimensions	77.0mm x 25.0mm x 123.0mm
Shipping weight	0.1kg
Tariff code	85444290

Classification

ipf product group	900
eClass 8.0	27279218
eClass 9.0	27060311
eClass 9.1	27060311
ETIM-5.0	EC001855
ETIM-6.0	EC001855
ETIM-7.0	EC001855

Connection

Dimensional drawing

Installation



Mounting / installation may only be carried out by a qualified electrician!

Disposal



Safety warnings

Before initial operation, please make sure to follow all safety instructions that may be provided in the product information. Never use these devices in applications where the safety of a person depends on their functionality. LED lighting systems can generate intensive UV radiation, which can damage your eyes in case of improper use. The manufacturer cannot be held responsible for damages that result from improper use or connection.