

External USB Sound Card 24 bit / 96 kHz Plug & Play for Windows, MAC, Linux, Chrome OS

Description

The sound adapter by Delock expands a computer, laptop or tablet-PC with an **additional external sound card**.

Compact High-Res Sound

The stereo **3.5 mm jack output** offers a maximum **sampling rate** of **24 Bit / 96 kHz**, so you can listen to your favorite music in **High-Res Audio** quality.

Microphone connector

At the 3.5 mm jack microphone input of this adapter, for example, a PC microphone can be connected and therefore **high-quality** audio **recordings** with a maximum **sampling rate** of **24 bit / 48 kHz** can be created. This makes the adapter ideal for **video chats**, **streaming** and **gaming**.

Plug & Play

Due to USB Plug & Play, the adapter is immediately ready for use and no driver installation is necessary. The adapter works with all common operating systems such as **Windows**, **Mac OS**, **Chrome OS**, **Linux** and **Android**.



Item no. 65964

EAN: 4043619659647

Country of origin: China

Package: Retail Box

Technical details

- Connectors:
 - 1 x USB 2.0 Type-A male >
 - 1 x speaker 3.5 mm 3 pin stereo jack female
 - 1 x microphone 3.5 mm 3 pin mono jack female
- Up to 24 Bit / 96 kHz sampling rate for playback and 24 Bit / 48 kHz for recording
- USB audio device specification 1.0
- USB HID class 1.1
- USB bus powered
- LED indicator for activity
- Plug & Play
- Dimensions (LxWxH): ca. 27 x 24 x 12 mm

System requirements

- Android 10.0 or above
- Chrome OS 90.0 or above
- Linux Kernel 5.8 or above
- Mac OS 11.2.3 or above
- Windows 10/10-64/11
- Windows Server 2019
- PC or laptop with a free USB Type-A port

Package content

- USB sound adapter
- User manual

Images



General

Function:	Plug & Play
Specification:	USB Audio Device Class 1.0 USB HID class 1.1
Supported operating system:	Linux Kernel 5.8.0 or above Windows 10 32-Bit Windows 10 64-Bit Windows Server 2019 Android 10.0 or above Mac OS 11.2.3 or above Chrome OS 90.0 or above Windows 11
LED indicator:	Activity

Interface

Connector:	1 x USB 2.0 Type-A male
Connector 1:	1 x speaker 3.5 mm 3 pin stereo jack female
Connector 2:	1 x microphone 3.5 mm 3 pin mono jack female

Technical characteristics

Sample rate:	24 Bit / 96 kHz
--------------	-----------------

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de