



HPX DUCT TAPE 2200



HPX DUCT TAPE 2200 is a high-quality, single-sided duct tape for general use. Good adhesion on rough surfaces and easy to tear by hand. Do not use on painted surfaces.

Applications

- Applications on walls and wood.
- Suitable for rough surfaces.
- Sealing, packaging, bundling.
- Fastening of construction film.

Construction

Adhesive	natural rubber
Carrier	polyester/cotton cloth

Technical details

Thickness	0,24 mm
Adhesive strength	11 N/25 mm
Tensile strength	147 N/25 mm
Temperature resistance	+60°C
Short term temperature	+70°C
UV resistance	limited
Elongation	12%
Unwinding force	7,8 N/25 mm

Art. No.	width	length	colour	Pack.	EAN code
PD4825	48 mm	25 m	silver	20	5425014225556
PD4850	48 mm	50 m	silver	20	5425014225501
PE4850	48 mm	50 m	black	20	5425014225266
PD7550	75 mm	50 m	silver	12	5425014225525

Recommendations for use

Temperature: between +15°C and +30°C. The surface should be clean, dry, free of dust and grease. When applying, avoid touching the adhesive side of the tape to avoid affecting its performance. Apply pressure-sensitive tapes under maximum pressure to achieve the optimum pressure level. The indicated performance level is reached after an adhesion time of 24 hours at +23°C.

Storage and shelf life

Clean and dry in a well-ventilated area, preferably at a temperature between +10°C and +30°C. Stored under these

The above information is given in good faith, but the user should assure himself that the performance of the product is sufficient for the application. The quoted values are average and should not be taken as maximum or minimum values for specific purposes. Option Tape Specialties cannot be held responsible for product failure unless full testing has been carried out. The customer has to decide on the tape's suitability for the own application.



www.hpx.eu

Frankrijkstraat 8 | Zone Waas nummer 2529 | 9140 Temse - Belgium
Tel. : +32 (0)3 710 19 19 | Fax : +32 (0)3 711 34 64 | info@hpx.eu - www.hpx.eu
Latest version 03/05/2021



HPX DUCT TAPE 2200

conditions, the shelf life will be at least 24 months.

The above information is given in good faith, but the user should assure himself that the performance of the product is sufficient for the application. The quoted values are average and should not be taken as maximum or minimum values for specific purposes. Option Tape Specialties cannot be held responsible for product failure unless full testing has been carried out. The customer has to decide on the tape's suitability for the own application.



www.hpx.eu

Frankrijkstraat 8 | Zone Waas nummer 2529 | 9140 Temse - Belgium
Tel. : +32 (0)3 710 19 19 | Fax : +32 (0)3 711 34 64 | info@hpx.eu - www.hpx.eu

Latest version 03/05/2021