

Cable USB 3.0 pin header female 2.00 mm 19 pin > 2 x USB 3.0 Type-A female panel-mount 80 cm

Description

This cable by Delock allows the extension of a USB 3.0 connection and can be used to connect various devices. The female ports can be attached with two screws, e.g. to a slot bracket, a cable duct or an enclosure with the corresponding opening. This can be used to install a USB connector at an easily accessible position. The cable is most suitable for self-designed computer systems as well as the Mini PCIe module [95234](#) by Delock.



Item no. 85244

EAN: 4043619852444

Country of origin: China

Package: Zip poly bag

Technical details

- Connectors:
 - 1 x 19 pin USB 3.0 pin header female >
 - 2 x USB 3.0 Type-A female panel-mount
- Pitch distance: 2.00 mm
- Pin 20 = Key
- Screw type: M2
- Mounting hole: ca. 15.0 x 8.5 mm, screw hole pitch ca. 18.5 mm
- Cable gauge:
 - 28 AWG data line
 - 24 AWG power line
- Cable diameter: ca. 5.5 mm
- Gold-plated connectors
- Data transfer rate up to 5 Gbps
- Colour: black
- Length incl. connectors: ca. 80 cm

System requirements

- A free 2.00 mm USB 3.0 pin header

Package content

- USB panel-mount cable

Images



General

Specification:	USB 5 Gbps
----------------	------------

Interface

Connector 1:	1 x 20 pin USB 5 Gbps pin header female
Connector 2:	2 x USB 5 Gbps Type-A female

Technical characteristics

Data transfer rate:	5 Gbps
---------------------	--------

Physical characteristics

Pitch distance:	2.00 mm
Pin finishing:	gold-plated
Cable gauge:	28 AWG data line 24 AWG power line
Length:	80 cm
Colour:	black
Cable diameter:	5.5 mm

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de