



LogiLink®

USB-C Aluminum Car Charger

USB-A QC + USB-C PD Ports, 20 W

Art. No.: PA0228A



For Car & Truck

Charge As You Go!

Compact, lightweight and easy to use, ideal for on the go. This car charger is not only suitable for charging your USB devices, it also has a built-in emergency hammer for the car windows.



Emergency Hammer

Aluminum

20 W
USB-C PD

18 W
USB-A QC

Safety
Protections



*The specifications and pictures are subject to change without prior notice.
*All trade names referenced are the registered trademarks of their respective owners.



PA0228A



4 052792 079555

Made in China



Efficient High-Speed Charging

Fast charge 2 USB-enabled devices such as smartphones, smartwatches, tablets, headsets, digital cameras and much more.

 USB-C PD 3.0 **20 W** output

 USB-A QC 2.0 **18 W** output

Equipped with Window Hammer

Designed specifically to help vehicle occupants escape quickly in a crisis.

Safe and Reliable

Multiple protections including overcharge, overcurrent, overvoltage, overheat, overdischarge, overload and short circuit.

*Remove any device attached on the charger before starting the car to avoid damage to the electronic device.

*Please check your gadget power requirement and compatibility.



Specification:

Input	12 V/24 V DC 2.1 A max.
Outputs	USB-A: 5 V/3 A (15 W), 9 V/2 A (18 W), 12 V/1.5 A (18 W max.) USB-C: 5 V/3 A (15 W), 9 V/2.22 A (20 W), 12 V/1.67 A (20 W max.) USB-A + USB-C: 5 V/3 A (15 W max.) PPS: 3.3–5.9 V/3 A, 3.3–11 V/1.8 A Total output: 20 W
Efficiency	VI
Protections	Overcharge, over-discharge, overload, overheat, overvoltage, short circuit
LED Indicator	Steady green LED for power on and charging
Operating Temperature	0–40°C
Operating Humidity	25–90% RH non-condensing
Color	Silver
Dimensions	Ø2.75 x 6.55 cm
Weight	37.5 g

Package Contents:

- » 1x USB-C Car Charger
- » 1x User Manual

Package Information:

- » Packing Dimension: 75 x 40 x 95 mm
- » Packing Weight: 0.054 kg
- » Carton Dimension: 320 x 210 x 175 mm
- » Carton Q'ty: 40 pcs
- » Carton Weight: 2.86 kg



*The specifications and pictures are subject to change without prior notice.
 *All trade names referenced are the registered trademarks of their respective owners.



PA0228A



4 052792 079555

Made in China