

DVI Cable 18+1 male to 18+1 male angled 2 m

Description

This DVI cable by Delock can be used to connect a DVI monitor or a projector to the DVI interface of a PC or laptop.



Item no. 85902

EAN: 4043619859023

Country of origin: China

Package: Zip poly bag

Technical details

- Connectors:
 - 1 x DVI 18+1 male >
 - 1 x DVI 18+1 male angled
- DVI-D (Single Link)
- DVI connector with screws
- Cable gauge: 30 AWG
- Cable diameter: ca. 7.3 mm
- Copper conductor
- Contacts gold-plated
- Cable double shielded
- Data transfer rate up to 3.96 Gbps
- Resolution up to 1920 x 1200 @ 60 Hz
(depending on the system and the connected hardware)
- Colour: black
- Length incl. connectors: ca. 2 m

System requirements

- A free DVI interface

Package content

- DVI cable

Images



General

Style:	angled 90° both sides identical
--------	------------------------------------

Interface

Connector 1:	1 x DVI 18+1 male
Connector 2:	1 x DVI 18+1 male

Technical characteristics

Data transfer rate:	3.96 Gbps
Maximum screen resolution:	1920 x 1200 @ 60 Hz
Maximum refresh rate:	60 Hz

Physical characteristics

Pin finishing:	gold-plated
Conductor material:	copper
Cable gauge:	30 AWG
Length:	2 m
Colour:	black
Cable diameter:	7.3 mm

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de