

Antenna Cable SMA 90° jack bulkhead > MMCX 90° plug 10 cm 1.37 thread length 13 mm

Description

The antenna cable by Delock is suitable for connecting components of radio frequency technology.



Item no. 89626

EAN: 4043619896264

Country of origin: China

Package: Zip poly bag

Technical details

- Connectors:
 - 1 x SMA Jack 90° >
 - 1 x MMCX 90° plug
- Thread length: 13 mm
- Impedance: 50 Ohm
- Cable: coaxial
- Cable type: 1.37
- Cable attenuation: 2.5 dB @ 2.4 GHz per meter
- Cable colour: black
- Smallest bending radius: 9 mm
- Cable length incl. connectors: ca. 10 cm

System requirements

- Device with a free MMCX 90° jack or with SMA plug

Package content

- Cable
- Locking ring, nut, toothed washer
- Protective dust cap

Interface

Connector 1:	1 x SMA Jack 90°
Connector 2:	1 x MMCX 90° plug

Technical characteristics

Impedance:	50 Ω
------------	------

Physical characteristics

Thread length:	13 mm
Cable type:	1.37
Cable attenuation:	2.5 dB @ 2.4 GHz per meter
Cable length incl. connectors:	10 cm
Smallest bending radius:	9 mm
Cable diameter:	1.37 mm

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de

