



Mi BF 44

IP
44

- Ventilation flange
- (recommended) alignment: vertical

CONNECTION DATA

MECHANICAL PROPERTIES

Delivered accessories:

IP degree of protection:

Suitable for box wall:

(Recommended) alignment:

Fastening material

IP44

300 mm

Vertical

AMBIENT CONDITIONS

Application area:	Indoor installation
Maximum ambient temperature 24 h:	35 °C
Ambient temperature:	-5 °C up to +40 °C
Relative humidity:	≤ 50 % at 40 °C, ≤ 100 % at 25 °C

DIMENSIONS

Height:	300 mm
Width:	55 mm
Depth:	100 mm
Net weight:	0.246 kg

CERTIFICATES

conforming to the standards:	IEC 61439-2
------------------------------	-------------

SALES DATA

Product number:	20001262
EAN:	4012591117803
Pack unit:	1
Customs tariff number:	85371098
ETIM class:	DYNAMIC: EC000331 - Ventilation plate (enclosure/cabinet) ETIM-4.0: EC000331 - Ventilation plate (enclosure/cabinet) ETIM-5.0: EC000331 - Ventilation plate (enclosure/cabinet) ETIM-6.0: EC000331 - Ventilation plate (enclosure/cabinet) ETIM-7.0: EC000331 - Ventilation plate (enclosure/cabinet)

DRAWINGS

