


Plugs

LAS 30 Au



Product	LAS 30 Au
description	Laminated, shatter-proof plug with caged spring and tapering sleeve providing protection against kinking. Soldered connections up to 1.5mm ² , cable diameters up to 4.2mm. Gold-plated brass contact, gold-plated copper beryllium contact spring.
operating instruction	BA409
article-no. / *colour	9725187xx ● 00 black ● 01 red ● 02 blue ● 03 yellow ● 04 green Au
drawing	
	
technical data	
connection	solder connection
rated voltage ⁽¹⁾	30 VAC / 60 VDC
measurement cat. acc. to IEC 61010	O ⁽³⁾
rated current ⁽¹⁾ (consider derating curve)	32 A
material plug	brass, gold plated
housing material	PVC-P
temperature range acc. To IEC61010 ⁽²⁾	-25 °C to +70 °C
standard	IEC 61010

⁽¹⁾ for normal environmental conditions -5°C to +40°C

⁽²⁾ contact the manufacturer for applications at deviating temperature ranges

⁽³⁾ without rated measurement category, for other circuits that are not directly connected to mains

stand: 06.05.2019