

Adapter mini DisplayPort 1.1 male > DVI female Passive white

Description

This adapter by Delock enables the connection of an DVI monitor to the system via a free mini DisplayPort interface.



Item no. 65129

EAN: 4043619651290

Country of origin: China

Package: Retail Box

Technical details

- Connectors:
 - 1 x mini DisplayPort 20 pin male >
 - 1 x DVI 24+5 female with nuts
- Chipset: NXP PTN3361
- DVI-D (Single Link), VGA not wired
- DisplayPort 1.1 specification
- Passive converter (level shifter), suitable only for graphics cards with DP++ output
- Resolution up to 1920 x 1200 @ 60 Hz
(depending on the system and the connected hardware)
- Standby detection, standby enter into sleep mode automatically
- 1 x ferrite core
- Cable length without connectors: ca. 12 cm
- Colour: white
- OS independent, no driver installation necessary

System requirements

- One free mini DisplayPort DP++ female

Package content

- Adapter mini DisplayPort to DVI

Images



Interface

Connector 1:	1 x mini DisplayPort male
Connector 2:	1 x DVI 24+5 female with nuts

Technical characteristics

Chipset:	NXP PTN3361
Maximum screen resolution:	1920 x 1200 @ 60 Hz

Physical characteristics

Colour:	white
---------	-------

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de