

USB 10 Gbps Coaxial Cable USB Type-C™ male to Type-A female 50 cm

Description

This USB cable by Delock enables the connection between devices with a USB Type-A port, e.g. USB sticks, a mouse or an external HDD, and a PC or laptop with a USB Type-C™ port. The coaxial conductors allow an interference-free data transfer with up to 10 Gbps.



0.5 m

Item no. 60568

EAN: 4043619605682

Country of origin: China

Package: Zip poly bag

Technical details

- Connectors:
 - 1 x USB 10 Gbps USB Type-C™ male
 - 1 x USB 10 Gbps Type-A female
- Host = USB Type-C™; Device = USB Type-A
- Cable gauge:
 - 32 AWG data line
 - 26 AWG power line
- Resistor: 5.1 kΩ
- Cable diameter: ca. 4 mm
- Conductors: 4 x coaxial for SuperSpeed USB, 1 x Twisted Pair for USB 2.0
- Contacts gold-plated
- Data transfer rate up to 10 Gbps
- Colour: black
- Length incl. connectors: ca. 50 cm

System requirements

- PC or laptop with a free USB Type-C™ port
- Device with USB Type-A port

Package content

- USB cable

Images



General

Specification:	USB 10 Gbps
----------------	-------------

Interface

Connector 1:	1 x USB 10 Gbps USB Type-C™ male
Connector 2:	1 x USB 10 Gbps Type-A female

Technical characteristics

Data transfer rate:	10 Gbps
Resistor:	5.1 kΩ

Physical characteristics

Cable colour:	black
Cable length incl. connectors:	50 cm
Connector finishing:	nickel-plated
Pin finishing:	gold-plated
Conductors:	4 x coaxial 1 x Twisted Pair
Cable gauge:	32 AWG data line 26 AWG power line

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de