









NOTE :-

- 1) ALL EDGES ARE BURR FREE
- 2) NON DIMENSIONAL RADIUS - 2..3mm
- 3) TOLERANCE AS PER DIN ISO 2768-cL
- 4) ALL CORNERS ARE FILLET WELDED AND GRINDED (240 GRAINS)
- 5) FINISH - RAL GRAY 7001 STRUCTURED

PROPERTY OF RaychemRPG (P) LTD.
ALL RIGHTS RESERAVED AND/OR PHOTOCOPYING THIS DOCUMENT
TO A PERSON WITHOUT RaychemRPG (P)LTD. WRITTEN AUTHORIZATION IS PROHIBITED

Sr No.	Material	UOM	Qty	NO.	REV.NO.	DESCRIPTION	DATE	SIGN	NAME	CHECKED
1	Base Assembly		1							
1.1	Base	Nos	1							
1.2	Din Rail Mounting Channel	Nos	2							
1.3	Blind NutSert M5 - SS 304 (Large Flanged)	Nos	4							
1.4	Bottom Sealing Cap	Nos	4							
2	Lid Assembly		1							
2.1	Lid	Nos	1							
2.2	Sealing Gasket	m	1.09							
2.3	Plastics Insert for Screw	Nos	4							
2.4	Stud EN ISO 13918-PTM6x12- A2-50 - SS 304	Nos	1							
2.5	Oval Head Screw DIN 966 -M5x33 - SS 304	Nos	4							
				TITLE :-		JUNCTION BOX ASSEMBLY 300 x 300 x 121	DATE	SIGN	NAME	CHECKED
				MATERIAL		GI STEEL 1.5mm Thick	01/04/15		MANOJ	DRAWN
				FINISH		Powder Coated Grey RAL 7001	01/04/15		A.M.	CHECKED
									M.S.	APPROVED
				Raychem RPG (P) Limited		Ceat Mahal Annexe, Dr. Annie Besant Road , Worli , Mumbai 400030 Web : www.raychemrpg.com	SCALE	PARTNO.	DRG. NO.	
				ALL DIMENSION ARE IN MM			REV		GIJB10-A	
							00			