

Car charger USB Type-C™ PD 3.0 and USB Type-A with 63 W

Description

This USB car charger by Delock can be used to charge two USB devices. One port is equipped with a **USB Type-C™ Power Delivery (PD)**, thereby supported devices can be charged with up to **60 watt**. In addition, one **USB Type-A** port with fast charging technology up to 18 watt is available for smartphones.



Item no. 64108

EAN: 4043619641086

Country of origin: China

Package: Retail Box

Technical details

- Connectors:
 - 1 x USB Type-C™ female
 - 1 x USB Type-A female
- Input: DC 12 ~ 24 V
- Output:
 - USB Type-C™ Power Delivery (PD):
 - 5 V / 9 V / 12 V / 15 V / 3.0 A, 20 V / 3.0 A
 - 5 V / 9 V / 12 V / 15 V / 3.0 A, 20 V / 2.25 A (USB-C™ + USB-A)
 - USB Type-A:
 - 5 V / 3.0 A, 9 V / 2.0 A, 12 V / 1.5 A
- Output power: max. 63 W total
- Overload protection
- Over current protection
- Overheating protection
- Short circuit protection
- Bicolour LED:
 - blue / red: USB-A / USB-C™ PD
- Material: plastic
- Colour: black
- Dimensions (LxD): ca. 70 x 40 mm

Package content

- Car charger

Images



Physical characteristics

Housing colour:	black
Housing material:	Plastic
Diameter:	40 mm
Length:	70 mm

Power supply

Power supply type:	Car charger
Input voltage:	DC 12 - 24 V
Power supply output:	12.0 V / 3.0 A 15.0 V / 3.0 A 20.0 V / 3.0 A 5.0 V / 3.0 A 9.0 V / 3.0 A
Power supply connector:	1 x USB Type-A female 1 x USB Type-C™ female

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de