

# Ultra High Speed HDMI Cable 48 Gbps 8K 60 Hz red 3 m certified

## Description

This high-quality Ultra High Speed HDMI cable by Delock can be used to connect devices with an HDMI interface, such as televisions, Blu-ray players, monitors or projectors. By supporting a maximum bandwidth of 48 Gbps, content can be displayed in **8K Ultra HD** (7680 x 4320 @ 60 Hz) resolution.



3 m



**Item no. 85775**

EAN: 4043619857753

Country of origin: China

Package: Retail Box

### Dynamic HDR and Dolby® Vision support

Supporting Dynamic HDR and Dolby® Vision, the cable is ideal for home cinema and gaming applications. Colours are realistically displayed with impressive depth, brightness and contrast are optimally reproduced.

### Perfect sound with eARC support

The Delock HDMI cable supports **Enhanced ARC** (eARC). This allows HDMI devices such as Blu-ray players to be connected directly to the TV. The uncompressed audio signals are then transmitted directly and lossless to the connected sound system via the audio return channel.

## Technical details

- Connectors:
  - 1 x HDMI male >
  - 1 x HDMI male
- Certified Ultra High Speed HDMI cable
- Cable gauge: 29 AWG
- Cable diameter: ca. 6.1 mm
- Copper conductor
- Triple shielded cable
- Contacts gold-plated
- Transmission of audio and video signals
- Data transfer rate up to 48 Gbps
- Resolution up to:
  - 7680 x 4320 @ 60 Hz
  - 5120 x 2880 @ 120 Hz
  - 3840 x 2160 @ 240 Hz(depending on the system and the connected hardware)
- 3D support: up to 3840 x 2160 @ 120 Hz  
(depending on the system and the connected hardware)
- Supports the 21:9 cinema aspect ratio
- Supports 1080p HFR (High Frame Rate) 3D
- Supports colour sampling in 4:4:4, 4:2:2 and 4:2:0 format
- Supports Display Stream Compression 1.2 (DSC)
- Supports Dolby® Vision
- Supports Dynamic HDR
- Supports HDCP 1.4 and 2.2
- Supports Game Mode VRR
- Supports eARC
- Up to 32 audio channels for speakers
- Up to 1536 kHz audio sampling rate
- Supports Dolby® TrueHD and DTS-HD Master Audio™
- Supports dynamic adjustment of lip synchronicity for audio / video delays
- Supports CEC 2.0 control commands
- Colour: red
- Length incl. connectors: ca. 3 m

---

## System requirements

- A free HDMI interface

---

## Package content

- Ultra High Speed HDMI cable

## Images



## General

Specification:	Dolby® Vision HDCP 1.4 HDCP 2.2 HDMI 2.1 HDR10
Style:	both sides identical

## Interface

Connector 1:	1 x HDMI-A male
Connector 2:	1 x HDMI-A male

## Technical characteristics

Data transfer rate:	48 Gb/s
Maximum screen resolution:	7680 x 4320 @ 60 Hz

## Physical characteristics

Connector finishing:	gold-plated
Pin finishing:	gold-plated
Conductor material:	copper
Cable gauge:	29 AWG
Shielding:	triple
Length:	3 m
Colour:	black / red

## Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de