Easy 45 Module USB 2.0 Retractable Cable USB Type-A to USB Type-C™ white

Description

This Easy 45 retractable cable by Delock can be connected to a PC, laptop or power source with USB-A connector and can be used to transfer data or charge various devices with USB Type-C™ interface. The simple snap-in mechanism ensures that the module is firmly in place and can be easily removed if necessary.



Item no. 81318

EAN: 4043619813186

Country of origin: China

Package: White Box

Flexible

The USB 2.0 cable can be pulled out in six steps and thus offers different cable lengths, depending on requirements. If the cable is not needed, it is neatly rolled up and stowed away.

Easy 45 connects

Easy 45 is a variable, modular system that allows components such as sockets, HDMI or USB connections to be added according to your needs. The Easy 45 modules are standardised and can be mounted in various module holder or cable ducts. Easy 45 builds the interface between electrical, network and system installation and many peripheral devices such as TV, monitors, printers, laptops and much more.

Technical details

- Connectors:
  1 x USB 2.0 Type-A male
  1 x USB Type-C™ male
- Cable gauge:
  Charging cable: 24 AWG
  Data cable: 30 AWG
- Flat cable
- Maximum output current: 2 A
- Data transfer rate up to 480 Mbps
- Voltage: max. 5 V
- Length incl. connectors:
  USB-A Host-cable ca. 12 cm
  USB-C™ device-cable ca. 50 cm (extended)

All names and symbols mentioned here are property of the respective producer. Printing errors, changes and errors excepted. **© 2026 by Delock. All rights reserved.**

- Suitable for module holder Delock Easy 45
- Suitable for 45 mm cable duct with minimum depth 45 mm
- Module size: 22.5 x 45 mm
- Dimensions (LxWxH): ca. 45.0 x 22.5 x 47.0 mm
- Colour: white

System requirements

- Power source with a free USB Type-A port
- PC or laptop with a free USB Type-A port
- Device with USB Type-C™ port
- A free module port Delock Easy 45

Package content

- Easy 45 module retractable cable

Images





All names and symbols mentioned here are property of the respective producer. Printing errors, changes and errors excepted. **© 2026 by Delock. All rights reserved.**

General

Specification:	USB 2.0

Interface

Connector 1:	1 x USB 2.0 Type-A male
Connector 2:	1 x USB 2.0 Type-C™ male

Technical characteristics

Data transfer rate:	480 Mbps
Maximum current:	2 A
Voltage:	5 V

Physical characteristics

Connector color:	white
Length:	47 mm
Width:	22.5 mm
Colour:	RAL 9003 Weiß

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de

All names and symbols mentioned here are property of the respective producer. Printing errors, changes and errors excepted. **© 2026 by Delock. All rights reserved.**