

| Identification                       | Part No.              | Drawing     |                     |    |      |    | Dimensions in mm |
|--------------------------------------|-----------------------|-------------|---------------------|----|------|----|------------------|
| Cable gland for metric cable entries |                       | thread<br>M | cable diameter<br>D | SW | E    | Nm |                  |
|                                      |                       |             |                     |    |      |    |                  |
| Metal<br><br>                        | 19 00 000 5080        | 20          | 5 - 9 mm            | 22 | 24.4 | 10 |                  |
|                                      | 19 00 000 5082        | 20          | 6 - 12 mm           | 22 | 24.4 | 10 |                  |
|                                      | 19 00 000 5084        | 20          | 10 - 14 mm          | 24 | 26.5 | 10 |                  |
|                                      | 19 00 000 5090        | 25          | 9 - 16 mm           | 30 | 33.5 | 15 |                  |
|                                      | 19 00 000 5092        | 25          | 13 - 18 mm          | 30 | 33.5 | 15 |                  |
|                                      | 19 00 000 5094        | 32          | 13 - 20 mm          | 40 | 44   | 15 |                  |
|                                      | 19 00 000 5096        | 32          | 18 - 25 mm          | 40 | 44   | 15 |                  |
|                                      | 19 00 000 5097        | 40          | 20 - 26 mm          | 50 | 55   | 20 |                  |
|                                      | 19 00 000 5098        | 40          | 22 - 32 mm          | 50 | 55   | 20 |                  |
|                                      |                       |             |                     |    |      |    |                  |
| Thermoplastic, white<br><br>         | 19 00 000 5180        | 20          | 5 - 9 mm            | 24 | 26.4 |    |                  |
|                                      | 19 00 000 5182        | 20          | 6 - 12 mm           | 24 | 26.4 |    |                  |
|                                      | 19 00 000 5184        | 20          | 10 - 14 mm          | 27 | 29.8 |    |                  |
|                                      | 19 00 000 5190        | 25          | 9 - 16 mm           | 33 | 36.5 |    |                  |
|                                      | 19 00 000 5192        | 25          | 13 - 18 mm          | 33 | 36.5 |    |                  |
|                                      | 19 00 000 5194        | 32          | 13 - 20 mm          | 42 | 46.8 |    |                  |
|                                      | 19 00 000 5196        | 32          | 18 - 25 mm          | 42 | 46.8 |    |                  |
|                                      | 19 00 000 5197        | 40          | 20 - 26 mm          | 53 | 58.8 |    |                  |
|                                      | 19 00 000 5198        | 40          | 22 - 32 mm          | 53 | 58.8 |    |                  |
|                                      |                       |             |                     |    |      |    |                  |
| Cable gland for metric cable entries |                       | thread<br>M | cable diameter<br>D | SW | E    | Nm |                  |
|                                      |                       |             |                     |    |      |    |                  |
| Metal<br><br>                        | <b>19 00 000 5050</b> | 20          | 5 - 14 mm           | 24 | 26.5 | 10 |                  |
|                                      | <b>19 00 000 5051</b> | 25          | 11 - 20 mm          | 30 | 33.0 | 15 |                  |
|                                      | <b>19 00 000 5052</b> | 32          | 15 - 25 mm          | 36 | 39.5 | 15 |                  |
|                                      | <b>19 00 000 5053</b> | 40          | 20 - 32 mm          | 45 | 48.0 | 20 |                  |
|                                      | <b>19 00 000 5054</b> | 50          | 31 - 42 mm          | 57 | 61.0 | 30 |                  |
| Thermoplastic, grey<br><br>          | <b>19 00 000 5150</b> | 20          | 5 - 14 mm           | 24 | 26.7 | 8  |                  |
|                                      | <b>19 00 000 5151</b> | 25          | 11 - 20 mm          | 30 | 33.0 | 10 |                  |
|                                      | <b>19 00 000 5152</b> | 32          | 15 - 25 mm          | 36 | 39.5 | 12 |                  |
|                                      | <b>19 00 000 5153</b> | 40          | 20 - 32 mm          | 45 | 48.0 | 14 |                  |
| Thermoplastic, black<br><br>         | <b>19 00 000 5155</b> | 20          | 5 - 14 mm           | 24 | 26.7 | 8  |                  |
|                                      | <b>19 00 000 5156</b> | 25          | 11 - 20 mm          | 30 | 33.0 | 10 |                  |
|                                      | <b>19 00 000 5157</b> | 32          | 15 - 25 mm          | 36 | 39.5 | 12 |                  |
|                                      | <b>19 00 000 5158</b> | 40          | 20 - 32 mm          | 45 | 48.0 | 14 |                  |