

HC

XX
Number of contacts

X
Pitch

X
Lever

X
Color

X
Foot print

X

X

X

X

X

End Stackable
01 1 contacts
02 2 contacts
03 3 contacts
.. ..
24 24 contacts
(pitch 2.5&3.5)
12 12 contacts
(pitch 7.0)

0 3.5/.138"
1 7.0/.276"
B 2.5/.098"

0 Standard
2 High profile
(only pitch 2.5)

2 Red
(RAL 3001/D)
3 Orange
(RAL 2011/P)
5 Green
(RAL 6018/T)
8 Grey
(RAL 7004/P)
C Multiple colors

0 Double row center contact
link together with end cover
1 Side single row
2 Center single row
3 Double row side contact
link together with end cover

0000 Standard

Any special item by
customer request,
please contact sales
department.

G ROHS compliant
(lead<4%)
In copper alloy

H ROHS compliant
(lead<1000ppm)
In copper alloy