

7 Port USB 3.2 Gen 2 Hub with 4 USB Type-A and 3 USB Type-C™ Ports

Description

The USB hub by Delock can be connected via USB Type-C™ interface to a PC or laptop. It has **four USB Type-A connectors** as well as **three USB Type-C™ connectors**. Different USB devices such as HDD docking station, card reader, external enclosure etc. can be connected.

Supports SuperSpeed USB 10 Gbps

A maximum data transfer rate of up to USB 3.2 Gen 2 - 10 Gbps can be reached.



Item no. 64209

EAN: 4043619642090

Country of origin: China

Package: Retail Box

Technical details

- Connectors:
 - 1 x SuperSpeed USB 10 Gbps (USB 3.2 Gen 2) USB Type-C™ female
 - 4 x SuperSpeed USB 10 Gbps (USB 3.2 Gen 2) Type-A female
 - 3 x SuperSpeed USB 10 Gbps (USB 3.2 Gen 2) USB Type-C™ female
 - 1 x 5 V DC jack
- Data transfer rate up to:
 - SuperSpeed USB 10 Gbps,
 - SuperSpeed USB 5 Gbps,
 - Hi-Speed 480 Mbps,
 - Full-Speed 12 Mbps,
 - Low-Speed 1.5 Mbps
- LED indicator
- Power supply: Self-powered
- Electrical power per port:
 - USB Type-C™: max. 10 watt (5 V / 2 A)
 - USB Type-A: max. 7.5 watt (5 V / 1.5 A)
- Dimensions (LxWxH): ca. 120 x 65 x 12 mm
- Colour: black
- Plug & Play

Power supply specification

- Wall power supply
- Input: AC 100 ~ 240 V / 50 ~ 60 Hz / 0.6 A
- Output: 5 V / 4 A
- Ground outside, plus inside
- Dimensions:
 - inside: \varnothing ca. 2.1 mm
 - outside: \varnothing ca. 5.5 mm
 - length: ca. 10 mm

System requirements

- Mac OS 12.2.1 or above
- Windows 8.1/8.1-64/10/10-64/11
- iPad Air (4th Generation) or above
- iPad Pro (3rd Generation) or above
- Surface Pro 7
- Device with a free USB Type-C™ port or with a free Thunderbolt™ 3 port or
- Device with a free USB4™ port or with a free Thunderbolt™ 4 port

Package content

- Hub USB 3.2 Gen 2
- Cable USB-C™ male to USB-C™ male, length ca. 1 m
- Power supply
- User manual

Images



General

Supported operating system:	Surface Pro 7 Windows 10 32-Bit Windows 10 64-Bit Windows 8.1 32-Bit Windows 8.1 64-Bit iPad Pro (3rd Generation) or above iPad Air (4th Generation) or above Windows 11 Mac OS 12.2.1 or above
LED indicator:	1 x

Interface

Connector 1:	1 x USB 10 Gbps USB Type-C™ female
Connector 2:	4 x USB 10 Gbps Type-A female
Connector 3:	3 x USB 10 Gbps USB Type-C™ female
Connector 4:	1 x 5 V DC jack

Technical characteristics

Data transfer rate:	10 Gbps
---------------------	---------

Physical characteristics

Cable length:	1 m
Material:	Plastic
Length:	120 mm
Width:	65 mm
Height:	12 mm
Colour:	black

Power supply

Input voltage:	AC 100 - 240 V / 50 - 60 Hz / 0.6 A
----------------	-------------------------------------

Power supply output:	5.0 V / 4.0 A
Power supply connector:	DC male 5.5 mm x 2.1 mm

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de