

USB 2.0 Extension Cable 10 m active with 4 port Hub

Description

This USB extension cable by Delock can be connected to a USB port of your computer and enables an extension of 10 m. You can connect up to four USB devices to the Hub. In case these USB devices do not have an own power supply you may need an optional power supply, e.g. Navilock [41337](#), which can be connected to the Hub.



10 m

Item no. 82748

EAN: 4043619827480

Country of origin: China

Package: Retail Box

Technical details

- Connectors:
 - 1 x USB 2.0 Type-A male >
 - 4 x USB 2.0 Type-A female
 - 1 x 5 V DC jack
- Data transfer rate up to 480 Mbps
- For connection to an active USB port
- Connectors: gold-plated
- Cable length: ca. 10 m
- Dimensions of the hub (LxWxH): ca. 63 x 35 x 17 mm
- Plug & Play

Specification of power connector

- 5 V, ground outside, plus inside
- Dimensions:
 - inside: ø ca. 1.35 mm
 - outside: ø ca. 3.5 mm
 - length: ca. 9.5 mm
- Optional power supply: [Navilock 41337](#)

System requirements

- Mac OS 10.9 or above
- Linux Kernel 3.2 or above
- Windows Vista/Vista-64/7/7-64/8.1/8.1-64/10/10-64/11
- PC or laptop with a free active USB Type-A port

Package content

- USB 2.0 extension cable 10 m with hub

Images



General

Specification:	USB 2.0
----------------	---------

Interface

Connector 1:	1 x USB 2.0 Type-A female 1 x USB 2.0 Type-A male
Connector 2:	1 x 5 V DC jack

Technical characteristics

Data transfer rate:	480 Mbps
---------------------	----------

Physical characteristics

Connector finishing:	gold-plated
Length:	10 m

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de