

USB 5 Gbps Hub with 4 Ports + 1 Fast Charging Port with Switch and Illumination

Description

This solid USB hub by Delock with **metal housing** can be connected to a computer via the USB Type-A interface. It expands the computer by **4 USB Type-A** ports. Connected devices such as smartphones can be charged or data can be transferred at 5 Gbps.



Item no. 63262

EAN: 4043619632626

Country of origin: China

Package: Retail Box

Additional fast charging port

Another USB Type-A port offers the possibility to charge devices, such as smartphones with up to **2.4 A**.

LED illumination and switch

Each port can be turned on or off individually by using the switches. In addition, each USB Type-A port has a frame that lights up as soon as the port is activated.

Technical details

- Connectors:
 - 1 x USB 5 Gbps Type-B female
 - 4 x USB 5 Gbps Type-A female
 - 1 x USB Type-A charging port (max. 5 V / 2.4 A)
 - 1 x 12 V DC jack
- Chipset: Genesys Logic GL3510, GL888F
- Data transfer rate up to:
 - SuperSpeed USB 5 Gbps,
 - Hi-Speed 480 Mbps,
 - Full-Speed 12 Mbps,
 - Low-Speed 1.5 Mbps
- LED illumination on the USB Type-A ports
- Robust metal housing
- Power supply: Self-powered
- Dimensions (LxWxH): ca. 99 x 46 x 21 mm
- Colour: grey
- Plug & Play

Power supply specification

- Input: AC 100 ~ 240 V / 50 ~ 60 Hz / 0.3 A
- Output: 12 V / 1 A
- Ground outside, plus inside
- Dimensions:
 - inside: \varnothing ca. 2.1 mm
 - outside: \varnothing ca. 5.5 mm
 - length: ca. 10 mm

System requirements

- Chrome OS
- Linux Kernel 3.18 or above
- Mac OS 10.15.3 or above
- Windows 8.1/8.1-64/10/10-64/11
- PC or laptop with a free USB Type-A port

Package content

- Hub USB 5 Gbps
- 1 x cable USB 5 Gbps Type-A male to USB 5 Gbps Type-B male, length ca. 80 cm
- External power supply
- User manual

Images



General

Function:	Plug & Play
Supported operating system:	Chrome OS Linux Kernel 3.18 or above Mac OS 10.15.3 or above Windows 10 32-Bit Windows 10 64-Bit Windows 8.1 32-Bit Windows 8.1 64-Bit Windows 11
LED indicator:	5 x

Interface

Connector 1:	1 x USB 5 Gbps Type-B female
Connector 2:	4 x USB 5 Gbps Type-A female
Connector 3:	1 x USB Type-A charging port (max. 5 V / 2.4 A)
Connector 4:	1 x 12 V DC jack

Technical characteristics

Data transfer rate:	5 Gbps
---------------------	--------

Physical characteristics

Cable length:	80 cm
Material:	Aluminium
Length:	99 mm
Width:	46 mm
Height:	21 mm
Switch:	5 x
Colour:	grey

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de