



FP TS 36

- DIN rail
- DIN rail 35 x 15 mm, 306 mm long

CONNECTION DATA

MECHANICAL PROPERTIES

Delivered accessories:
Suitable for box size:

Fastening material
2, 4

AMBIENT CONDITIONS

Application area:
Maximum ambient temperature 24 h:
Ambient temperature:
Relative humidity:

Indoor installation
35 °C
-5 °C up to +40 °C
≤ 50 % at 40 °C, ≤ 100 % at 25 °C

MATERIAL PROPERTIES

Material:
Surface treatment:

Steel
Sendzimir galvanised

DIMENSIONS

Height: 15 mm
Width: 35 mm
Net weight: 0.205 kg
Length: 306 mm
Material thickness: 1.5 mm

CERTIFICATES

conforming to the standards:

IEC 61439-3, DIN EN 60715

SALES DATA

Product number:	68000045
EAN:	4012591104445
Pack unit:	1
Customs tariff number:	85371098
ETIM class:	DYNAMIC: EC001285 - Mounting rail for electrical/industrial control equipment ETIM-9.0: EC001285 - Mounting rail for electrical/industrial control equipment ETIM-8.0: EC001285 - Mounting rail for electrical/industrial control equipment ETIM-7.0: EC001285 - Mounting rail for electrical/industrial control equipment ETIM-6.0: EC001285 - Mounting rail for electrical/industrial control equipment ETIM-5.0: EC001285 - Mounting rail for electrical/industrial control equipment ETIM-4.0: EC001285 - Mounting rail for electrical/industrial control equipment

DRAWINGS

