

Ferrite

(See page 92 for material characteristics)

Ferrite Shallow Pots with Hook

- Max. operating temperature: 120°C
- Mild steel pot painted white
- Ideal for retail or general display applications
- For hanging graphics, utensils, tools etc



Product Number	Diameter mm	Thickness mm	Height mm	Thread	Weight g	Pull Force kg	Units / Pack
E879-RB	25	34	8	M4	27	4.0	1
E880-RB	32	34	8	M4	34	8.0	1
E881-RB	36	34	8	M4	38	10.0	1

Ceiling Magnet with Hook

- Simple solution for hanging display materials
- Can be attached/removed quickly with no marking



Product Number	Length mm	Width mm	Height mm	Thread	Weight kg	Pull Force kg	Units / Pack
CM3429	34	29	12	M4	0.04	6	1
CM5715	57	15	24	M4	0.05	11.5	1
CM5327	53	27	12	M4	0.06	15	1

Ferrite Shallow Pot Magnet with 2 Hooks

- Suitable for keys, signs, or light clothing, etc.
- Ideal for a production area, workshop, schools, storage
- Tough casing made of galvanised steel with plastic coating
- With locking screw made of shatter-proof plastic front



Product Number	Diameter mm	Pot Height incl. Ferrule mm	Hook Length (to the centre) L1/L2 mm	Unit Weight g	Pull Force g	Unit/ Packs
E1080/B	58	26.5	53 / 83	180	11	1