

USB 5 Gbps Hub with 2 x USB Type-A and 2 x USB Type-C™ female and 1 x Fast Charging Port + Switch

Description

This solid USB hub by Delock with **metal housing** can be connected to a computer, laptop or mobile device via the **USB Type-A or USB-C™** interface. It expands the computer by **four USB ports**. Different USB devices such as USB flash memory, card reader, external enclosure etc. can be connected. A maximum data transfer rate of up to **5 Gbps** can be reached.

Additional fast charging port

Another USB Type-A port offers the possibility to charge devices, such as smartphones with up to **2.4 A**.

Extensive connectivity

Due to the **specially designed adapter**, the Delock hub can be quickly and easily connected to the USB Type-A socket. Thus, it can be easily connected to new devices with USB Type-C™ female and older devices that only have a USB Type-A connector. The **adapter is located directly on the cable** and therefore it cannot be lost.



Item no. 64248

EAN: 4043619642489

Country of origin: China

Package: Retail Box

Technical details

- Connectors:
 - 1 x USB 5 Gbps USB Type-C™ female
 - 2 x USB 5 Gbps Type-A female
 - 2 x USB 5 Gbps USB Type-C™ female
 - 1 x USB Type-A charging port (max. 5 V / 2.4 A)
 - 1 x 12 V DC jack
- Data transfer rate up to 5 Gbps
- 5 x LED indicator
- Robust metal housing
- Power supply: Bus-powered or Self-powered
- Dimensions (LxWxH): ca. 115 x 47 x 23 mm
- Colour: grey
- Plug & Play

Power supply specification

- Input: AC 100 ~ 240 V / 50 ~ 60 Hz / 1.3 A
- Output: 12.0 V / 3.0 A / 36.0 W
- Ground outside, plus inside
- Dimensions:
 - inside: \varnothing ca. 2.1 mm
 - outside: \varnothing ca. 5.5 mm
 - length: ca. 10 mm

System requirements

- Android 11.0 or above
- Chrome OS
- Linux Kernel 5.15 or above
- Mac OS 12.4 or above
- Windows 10/10-64/11
- iPad Air (4th Generation) or above
- iPad Pro (3rd Generation) or above
- Surface Pro 7
- A free USB Type-A female port or
- A free USB Type-C™ female port

Package content

- Hub USB 5 Gbps
- Cable USB-C™ male to USB-C™ male (with adapter to USB Type-A male), length ca. 60 cm
- External power supply
- User manual

Images



General

Function:	Plug & Play
Supported operating system:	Chrome OS Surface Pro 7 Windows 10 32-Bit Windows 10 64-Bit iPad Pro (3rd Generation) or above iPad Air (4th Generation) or above Windows 11 Mac OS 12.4 oder höher Android 11.0 or above Linux Kernel 5.15 or above
LED indicator:	5 x

Interface

Connector 1:	1 x USB 5 Gbps USB Type-C™ female
Connector 2:	2 x USB 5 Gbps USB Type-C™ female
Connector 3:	2 x USB 5 Gbps Type-A female
Connector 4:	1 x USB Type-A charging port (max. 5 V / 2.4 A)
Connector 5:	1 x 12 V DC jack

Technical characteristics

Data transfer rate:	5 Gbps
---------------------	--------

Physical characteristics

Housing material:	metal
Length:	115 mm
Width:	47 mm
Height:	23 mm
Switch:	5 x
Colour:	grey

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de