
Keystone Module RJ12 jack > LSA Cat.3 UTP black

Description

This module by Delock can be used to connect a telephone cable to an RJ12 female port. With its standardised dimensions it can be used for easy snap-in mounting in e.g. a Keystone patch panel, face plate or surface-mount box.





Item no. 86468

EAN: 4043619864683

Country of origin: China

Package: Zip poly bag

Technical details

- Connectors:
  external: 1 x RJ12 (RJ25) jack (6P/6C) >
  internal: LSA (toolfree)
- Compatible with RJ11 (6P/2C) and RJ14 (6P/4C)
- Unshielded (UTP)
- For solid or stranded wire up to 0.511 mm (24 - 26 AWG)
- For Keystone ports with 19.2 x 14.9 mm
- Colour: black
- Dimensions (LxWxH): ca. 27.4 x 19.8 x 19.8 mm

Package content

- Keystone module
- Cable manager

All names and symbols mentioned here are property of the respective producer. Printing errors, changes and errors excepted. **© 2026 by Delock. All rights reserved.**

Images



All names and symbols mentioned here are property of the respective producer. Printing errors, changes and errors excepted. **© 2026 by Delock. All rights reserved.**

General

Suitable for conductor gauge:	24 - 26 AWG
Mounting type:	Keystone module

Interface

External:	1 x RJ12 jack
Internal:	1 x LSA block

Physical characteristics

Housing colour:	black
Shielding:	unshielded
Length:	27.4 mm
Width:	19.8 mm
Height:	19.8 mm

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de

All names and symbols mentioned here are property of the respective producer. Printing errors, changes and errors excepted. **© 2026 by Delock. All rights reserved.**